

TECHSPEC® 50mm Dia. x 150mm FL 785nm V-Coat, UV PCX Lens



Stock **#25-923** **4 In Stock**

⊖ 1 ⊕ £267²⁰

ADD TO CART

Volume Pricing	
Qty 1-5	£267.20 each
Qty 6-25	£213.60 each
Qty 26-49	£200.80 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Plano-Convex Lens **Type:**

Physical & Mechanical Properties

50.00 +0.0/-0.025 **Diameter (mm):**

Protective as needed **Bevel:**

7.00	Center Thickness CT (mm):
<1	Centering (arcmin):
49	Clear Aperture CA (mm):
2.29	Edge Thickness ET (mm):

Optical Properties

150.00 @ 587.6nm	Effective Focal Length EFL (mm):
Fused Silica	Substrate: <input type="checkbox"/>
3	f#:
0.17	Numerical Aperture NA:
785nm V-Coat	Coating:
145.20	Back Focal Length BFL (mm):
$R_{abs} < 0.25\%$ @ 785nm	Coating Specification:
785	Design Wavelength DWL (nm):
±1	Focal Length Tolerance (%):
68.77	Radius R ₁ (mm):
40-20	Surface Quality:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

- <0.25% Reflection at 785nm
- 5 - 50mm Diameters Available
- 10 - 250mm EFL Designs Available
- [405nm](#), [532nm](#), [1064nm](#), and [1550nm](#) V-Coated Options Offered

TECHSPEC® Laser Line Coated Fused Silica PCX Lenses are available in a variety of laser line V-Coat AR coating options. Designed for maximum throughput at the specified laser wavelength, these lenses are ideal for applications utilizing low power HeNe, Diode, and Nd:YAG laser sources. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components.