

TECHSPEC® 50mm Diameter 70R/30T, VIS λ/10 Plate Beamsplitter



TECHSPEC® λ/10 Plate Beamsplitters

Stock #34-417 **20+ In Stock**

⊖ 1 ⊕ £247.⁷⁷

ADD TO CART

Volume Pricing	
Qty 1-5	£247.77 each
Qty 6-49	£197.86 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Standard Beamsplitter **Type:**

Physical & Mechanical Properties

Plate	Construction:
50.00	Diameter (mm):
±0.10	Dimensional Tolerance (mm):
Protective Bevel as needed	Edges:
3.00 ±0.20	Thickness (mm):
30 arcmin	Wedge Angle (arcmin):

Optical Properties

Coating Specification:	
Surface 1: 70/30 ±5% @ 550nm, ±10% @ 400 - 700nm	
Surface 2: AR $R_{avg} \leq 1\%$, $R_{abs} \leq 2\%$ @ 400 - 700nm	
Reflection/Transmission Ratio (R/T):	
70/30	
Fused Silica (Corning 7980)	Substrate: <input type="checkbox"/>
$\lambda/10$	Surface Flatness (P-V):
20-10	Surface Quality:
400 - 700	Wavelength Range (nm):

Regulatory Compliance


Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

PRODUCT DETAILS

- 30 Arcminute Wedge to Minimize Internal Interference
- Wide Range of Splitting Ratios
- Fused Silica Substrate

TECHSPEC® $\lambda/10$ Plate Beamsplitters are designed for use with a 45 degree angle of incidence and random polarization. With a featured 30 arcminute wedge, the effects of internal interference are minimized. Each beamsplitter also includes a multi-layer anti-reflection (AR) coating on the back-surface. TECHSPEC® $\lambda/10$ Plate Beamsplitters have been optimized for the visible spectrum and are offered in a variety of splitting ratios. These beamsplitters are ideal for laser applications due to the wedged design and high quality Fused Silica substrate.

TECHNICAL INFORMATION



CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

COMPATIBLE MOUNTS
