

## 75 x 75mm, Rhodium Coated First Surface Mirror



Rhodium Coated First Surface Mirrors

Stock **#15-494** **2 In Stock**

⊖ 1 ⊕ £97<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	£97.60 each
Qty 6-49	£78.40 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

Flat Mirror **Type:**

#### Physical & Mechanical Properties

3.00 ±0.20 **Thickness (mm):**

75.0 x 75.0 **Dimensions (mm):**

Protective as needed	<b>Bevel:</b>
±0.25	<b>Dimensional Tolerance (mm):</b>
Seamed	<b>Edges:</b>
75.00	<b>Length (mm):</b>
75.00	<b>Width (mm):</b>

## Optical Properties

Metal	<b>Coating Type:</b>
Rhodium (400-10000nm)	<b>Coating:</b>
4 - 6λ	<b>Surface Flatness (P-V):</b>
400 - 10000	<b>Wavelength Range (nm):</b>
Float Glass	<b>Substrate:</b> <input type="checkbox"/>
R <sub>avg</sub> >70% @400 - 700nm R <sub>avg</sub> >90% @2000 - 10,000nm	<b>Coating Specification:</b>
80-50	<b>Surface Quality:</b>

## Environmental & Durability Factors

Severe, per MIL-C-675C Paragraph 3.8.4.1	<b>Coating Abrasion:</b>
ML-PRF-13830B, App B Para. 4.4.6	<b>Coating Adhesion:</b>

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 247:</b>

### Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Corrosion and Extreme Abrasion Resistant Rhodium Coating
- High Reflectivity in the VIS and IR
- Ideal for Orthodontic Applications

Rhodium Coated First Surface Mirrors provide high reflectivity and are ideal for orthodontic applications, especially in intra-oral photography. These mirrors feature a rhodium coating, which is an element notably resistant to corrosion and aggressive chemicals and passes severe abrasion tests as per MIL-C-675C. Rhodium Coated First Surface Mirrors utilize a float glass substrate which enables easy customization and provides excellent cost to performance ratio. They are available in standard metric sizes, with either circular or square geometries.

## Compatible Mounts