

# 75mm Dia. Broadband Hybrid Diffuser



Broadband Hybrid Diffusers

Stock **#36-678** 20+ In Stock

-

1

+

£53<sup>20</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | £53.20 each                   |
| Qty 11-49      | £42.40 each                   |
| Need More?     | <a href="#">Request Quote</a> |

 Prices shown are exclusive of VAT/local taxes

Product Downloads

| Physical & Mechanical Properties |                                                                                           |
|----------------------------------|-------------------------------------------------------------------------------------------|
| 75.00 ±0.5                       | Diameter (mm):                                                                            |
| 120                              | Grit:  |
| 1.75 ±0.1                        | Thickness (mm):                                                                           |
| Optical Properties               |                                                                                           |

|                       |                                     |
|-----------------------|-------------------------------------|
| Uncoated              | Coating:                            |
| White Diffusing Glass | Substrate: <input type="checkbox"/> |
| 400 - 1100            | Wavelength Range (nm):              |
| Regulatory Compliance |                                     |
| Compliant             | RoHS 2015:                          |
| Compliant             | Reach 211:                          |
| View                  | Certificate of Conformance:         |

## Product Details

- Surface Treated Semi-Opaque White Glass
- Two Mechanisms of Scatter
- Excellent Scattering into the NIR

Broadband Hybrid Diffusers are semi-opaque diffusers designed to scatter efficiently from the UV to the NIR. Featuring surfaces sandblasted with 120-grit and a 1.75mm thick scattering medium, these diffusers uniquely offer two mechanisms of scatter. Each scatter mechanism has its own wavelength dependency, and when combined on a single optic, produce a diffuser that scatters across a wide spectral region. Broadband Hybrid Diffusers are ideal for applications that require high scatter for even illumination and can be used as view screens.

## Compatible Mounts