

[See all 33 Products in Family](#)

## DALSA Genie Nano Cable Kit

See More by [Teledyne DALSA](#)



Dalsa Genie Nano Cable Kit, #34-967



Stock **#34-967** **1 In Stock**

⊖ 1 ⊕ £147<sup>20</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	£147.20 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Camera Accessory

Type:

**Contents of Kit:**  
12V Power Supply, 2m GigE Cable, and 2m Breakout Cable

Note:

Included in Kit:  
· 12V Power Supply with Genie Nano Aux Connector (Samtec 10-pin), 4m  
· RJ-45 Ethernet Cable, 2m  
· GPIO Cable, Genie Nano Aux (Samtec 10-pin) to breakout Euroblock Connector, 2m

---

## Regulatory Compliance

[Compliant](#) **REACH 201:**

[View](#) **Certificate of Conformance:**

---

## Product Details

- TurboDrive™ Technology Achieve Frame Rate up to 800 fps
- Compact, Lightweight, Robust All Metal Body
- Global Electronic Shutter with Exposure Control and Advanced Feature Set



Teledyne  
Authorized  
Distributor

Teledyne DALSA Genie™ Nano GigE Cameras are available in a range of Sony Pregius and On Semiconductor CMOS sensors. These GigE PoE cameras provide high speed, low noise, and global electronic shutters. The proprietary TurboDrive™ technology allows the Genie™ Nano to exceed standard frame rates, delivering up to 800 fps while retaining full image quality. These cameras come with a host of advanced feature set such as multi ROI windows and Burst Acquisition, which utilizes onboard memory buffer to achieve even faster frame rates.\* Teledyne DALSA Genie™ Nano GigE Cameras are packaged in compact and robust all metal housing, making them ideal for electronics inspection, industrial metrology, and Intelligent Traffic Systems (ITS) applications.

**Note:** Frame rates achievable through TurboDrive™ or Burst Acquisition could vary with factors such as image quality and resolution.

**Sapera LT** is a free image acquisition and control software development toolkit (SDK) for Teledyne DALSA'S 1D cameras / 2D cameras / 3D Laser Profiler cameras and frame grabbers. Hardware independent in nature, Sapera LT offers a rich development ecosystem for machine vision OEMs and system integrators. Sapera LT supports image acquisition from cameras and frame grabbers based on machine vision standards including GigE Vision™, CameraLink®, CameraLink HS™, CoaXpress®, and USB3 Vision™.

---