

[See all 8 Products in Family](#)

**TECHSPEC® Cobalt Series High Mag Kit, C Mount**



SilverTL™ Telecentric Lenses



Stock #73-083 [CONTACT US](#)

- 1 + £5,604<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	£5,604.00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Contents of Kit:

- [88-603](#)
- [15-872](#)
- [62-901](#)
- [89-721](#)
- [63-233](#)
- [56-025](#)

Included Focal Lengths or Magnifications:

0.55, 0.69, 0.9

## Optical Properties

0.55, 0.69, 0.9

Included F#:

## Regulatory Compliance

[View](#)

Certificate of Conformance:

## Product Details

- Easy to Order Kits of Our Best Selling Telecentric Imaging Lenses
- Various Magnification and Working Distance Kits Available
- TECHSPEC [SilverTL](#), [VariMagTL](#), and [CompactTL](#)

TECHSPEC® Telecentric Imaging Lens Kits provide sets of TECHSPEC® [SilverTL](#), [VariMagTL](#), and [CompactTL](#) Imaging Lenses in easy to order kits at a reduced price. These kits offer multiple solutions to applications requiring telecentric lenses including machine vision, metrology, automotive and electronic inspection, measurement, and gauging. TECHSPEC® Telecentric Imaging Lens Kits offer various selections of magnifications and working distances within the product lines. The TECHSPEC® [SilverTL](#), [VariMagTL](#), and [CompactTL](#) lenses in these kits are C-Mount camera compatible, and feature a locking iris and focus adjustment to prevent unwanted adjustments.

- [SilverTL](#): Silver Telecentric, Metrology and Gauging
- [VariMagTL](#): Variable Magnification Telecentric, Adjustable Magnification That Can Be Locked with a Set Screw
- [CompactTL](#): Compact Telecentric, C-Mount Lenses for Machine Vision, Factory Floors, Assembly Lines