

Coherent® Beam Position Thermopile Power Sensors 1098320 | 100mW-45W

See More by [Coherent®](#)



Stock #12-398 [CONTACT US](#)

⊖ 1 ⊕ £1,328⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£1,328.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Model Number:
LM45 HTD Coherent Part Number: 1098320

Meter required **Type:**

Linearity (%)
±1

Calibration Uncertainty (%)
±2

0.5 - 10 **Long Pulse Joule Mode Range (J):**

±3 **Long Pulse Joule Mode Accuracy (%):**

Air **Cooling Method:**

[#35-203](#), [#12-393](#), [#59-978](#),
[#88-411](#), [#66-277](#), [#88-412](#) **Compatible Meters:**

Physical & Mechanical Properties

19 **Active Area Diameter (mm):**

Optical Properties

10,600 **Calibration Wavelength (nm):**

0.25 - 10.6 **Wavelength Range (µm):**

Sensor

Quad Element Thermopile **Type of Sensor:**

Electrical

±1.5 **Spectral Compensation Accuracy (%):**

45 **Maximum Incident Beam Power (W):**

Hardware & Interface Connectivity

2.5 **Length of Cable (m):**

DB-25 **Computer Interface:**

Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[Contains SVHC\(s\)](#) **Reach 224:**

[View](#) **Certificate of Conformance:**

Product Details

- Thermopile Detector Element for High Power Measurements
- Measure Beam Position on Detector Surface
- ISO 17025 Certified

Coherent® Beam Position Sensing Thermopile Power Sensors are all-purpose sensors designed to measure the average power or energy of a wide variety of continuous wave or pulsed lasers. Coherent Beam Position Sensing Thermopile Power Sensors utilize a quadrant thermopile detector disk to sense the position of the laser beam on the detector surface while measuring the laser power. Coherent thermopile sensors can operate across a wide range of input powers, and do not saturate.

Note: The LM-20 is designed for embedded use and must be mounted on a heat sink.