

[See all 15 Products in Family](#)

Coherent® EnergyMax 1110746 | 500μJ-1000mJ, DB25

See More by [Coherent®](#)



Coherent® EnergyMax Laser Energy Sensors

Stock **#12-386** [CONTACT US](#)

-

1

+

£1,408^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	£1,408.00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Model Number:	
J-25MB-HE Coherent Part Number: 1110746	
Type:	
Meter required	
Linearity (%):	
±3	
Calibration Uncertainty (%):	
±2	

<16	Noise Equivalent Energy (μJ):
#35-203 or #66-277	Compatible Meters:

500mJ/cm² (10ns, 1064nm)	Maximum Incident Energy Density:
500μJ - 1J	Energy Range:

#88-412	Preferred Meter:
---------	------------------

Physical & Mechanical Properties

25	Active Area Diameter (mm):
----	----------------------------

Optical Properties

1064	Calibration Wavelength (nm):
------	------------------------------

17	Maximum Pulse Width (μs):
----	---------------------------

190 - 12000	Wavelength Range (nm):
-------------	------------------------

Sensor

Pyroelectric	Type of Sensor:
--------------	-----------------

Electrical

1000	Maximum Repetition Rate (pps):
------	--------------------------------

5	Maximum Incident Beam Power (W):
---	----------------------------------

Hardware & Interface Connectivity

DB25	Connector:
------	------------

2.5	Length of Cable (m):
-----	----------------------

Regulatory Compliance

Exempt	RoHS 2015:
--------	------------

Contains SVHC(s)	Reach 224:
------------------	------------

View	Certificate of Conformance:
------	-----------------------------

Product Details

- ISO 17025 Certified
- Embedded Spectral Compensation Characteristics
- Automatic Temperature Compensation

Coherent® EnergyMax Laser Energy Sensors are designed for a variety of demanding laser measurement applications. These energy sensors, available in meter or meterless USB configurations, incorporate a diffuse coating to minimize specular reflection and feature large active areas. The J-50MB-YAG combines the MaxBlack coating with a diffuser for use with high energy lasers of up to 3J. Coherent® EnergyMax Laser Energy Sensors utilize onboard sensors to automate temperature compensation for improved measurement accuracy.