

Coherent® Fan-Cooled Thermopile Sensor PM200F-50 1098472 | 200W Max Power

See More by [Coherent®](#)



Coherent® Fan-Cooled Thermopile Sensors

Stock **#12-402** **1 In Stock**

-

1

+

£1,968^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	£1,968.00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
1098472	Model Number:
Meter required	Type:
1	Calibration Uncertainty (%):
Fan	Cooling Method:

Compatible Meters: #35-203 , #12-393 , #59-978 , #88-411 , #66-277 , #88-412	
Physical & Mechanical Properties	
50	Active Area Diameter (mm):
102 x 102 x 114	Dimensions (mm):
Optical Properties	
514	Calibration Wavelength (nm):
250 - 11000	Wavelength Range (nm):
0.25-11	Wavelength Range (µm):
Electrical	
0.1	Power Resolution (W):
1W-200W	Power Range:
200	Maximum Power (W):
1	Minimum Power (W):
Hardware & Interface Connectivity	
DB-25	Computer Interface:
Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

Product Details

- Designed to Measure Laser Power up to 300W
- Ideal for Applications where Water-Cooling is Not Possible
- Compact Size for Portability and Use in Field Applications

Coherent® Fan-Cooled Thermopile Sensors are an excellent option for measuring high-powered lasers in environments where water-cooled thermopile sensors cannot be used. The fan cooling system makes it possible for these thermopile sensors to provide continuous power monitoring of lasers up to 300W. Additionally, the large 50mm aperture size allows for easy laser alignment for quick data acquisition. Coherent® Fan-Cooled Thermopile Sensors feature a compact size and easy set up procedure, making them ideal for use in the field or production testing. The high power resolution of these sensors ensures that accurate measurements are made for their large range of accepted laser powers.