

[See all 4 Products in Family](#)

70mm, Compact Motorized Rotation Stage, Metric



70mm, Compact Motorized Rotation Stage

Stock **#23-929** **10 In Stock**

⊖ 1 ⊕ £780⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	£780.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Metric **Type:**

Controller Required: [#23-931](#) **Note:**

Stepper Motor **Type of Motor:**

Physical & Mechanical Properties

Type of Movement:

Rotary	Guide System:
Ball Bearing	
	Travel (°):
360	
	Accuracy (°):
0.03	
	Backlash (°):
0.2	
	Construction:
Aluminum, 3D Printed Plastic	
	Height (mm):
44.7	
	Load Capacity (kg):
0.5	
	Repeatability (°):
0.03	
	Speed (°/s):
240	
	Weight (kg):
0.25	
	Table Diameter (mm):
70	
	Parallelism (°):
0.0083	
	Min. Incremental Movement (°):
0.02	

Optical Properties

	Resolution (µm):
0.02°	

Electrical

	Maximum Operating Current (mA):
500	

Hardware & Interface Connectivity

	Type of Drive:
Gear Transmission	
	Computer Interface:
USB-C	

Threading & Mounting

	Mounting Threads:
(4) M6 x 1.0, (4) M3 x 0.5, (8) M2 x 0.4	

Environmental & Durability Factors

	Operating Temperature (°C):
10-40	

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

Product Details

- Compact Footprint and Economic Price Point
- Light-weight Housing with Durable Stage Platform
- Compatible with [TECHSPEC Stages](#)
- Use Power Supply [#21-075](#) to Power Controller [#23-931](#)

Compact Motorized Rotation Stages are a cost-effective solution for motorized rotation adjustment within an optical system. These stages feature an anodized aluminum stage platform for precision mounting, with a preinstalled breadboard mounting plate. The compact overall footprint maximizes space efficiency to add motorization to space constrained systems. Compact Motorized Rotation Stages share the same hole patterns as our [TECHSPEC stages](#), making them an ideal lab bench component for motorized system building. Requires a Controller, [#23-931](#), which can be easily connected via an included 1m USB-C to USB-A cable.