

## 0.12mm Dia., TO-46 Package, InGaAs Photodiode



InGaAs Photodiodes (FC Receptacle , TO-5, TO-46)

Stock #55-754 **10 In Stock**

⊖ 1 ⊕ £80<sup>40</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-4	£80.40 each
Qty 5-9	£69.20 each
Qty 10-24	£63.60 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Ball Lens **Type of Optics:**

InGaAs Photodiode **Type:**

0.3 **Rise/ Fall Time @ V<sub>R</sub>=5V (ns):**

TO-46

Package:

## Physical & Mechanical Properties

Active Area Diameter (mm):  
0.12

## Optical Properties

Spectral Response (nm):  
900 - 1700

## Electrical

Responsivity @ 1310nm (AW):  
0.8 minimum / 0.9 typical

Responsivity @ 1550nm (AW):  
0.9 minimum / 0.95 typical

Capacitance @  $V_R=5V$  (pF):  
2 typical

Noise Equivalent Power NEP ( $W/Hz^{1/2}$ ):  
 $4.5 \times 10^{-15}$

Maximum Forward Current (mA):  
5

Maximum Reverse Current (mA):  
2

Maximum Reverse Voltage (V):  
20

Dark Current @  $V_R=5V$  (nA):  
0.05 typical / 2 maximum

## Regulatory Compliance

Certificate of Conformance:  
[View](#)


## Product Details

- Response Range From 900nm to 1700nm
- Both Small Area (High Speed) and Large Area
- [Segmented InGaAs Photodiodes](#) Also Available


InGaAs Photodiodes feature excellent responsivity from 900nm to 1700nm with active areas ranging from 0.07mm to 3.0mm. Photodiodes with active area sizes less than 1mm provide low capacitance, low dark current, and high responsivity from 1100nm to 1620nm, for high speed datacom and telecom applications. Photodiodes with active area sizes of 1mm and up provide large active areas, low noise, and high shunt resistance enabling high sensitivity for weak signals. InGaAs Photodiodes are isolated in TO-46, TO-18, or TO-5 packages with either a ball lens or double-sided AR coated window, depending on the packaging. These photodiodes are ideal for a multitude of research and OEM applications including IR laser alignment, medical diagnostics, and chemical analysis.

**Note:** To ensure well centered incident light, a [focusing lens](#) or [pinhole](#) is recommended due to inhomogeneity at the edge of the photodiode chip which can cause a decrease in detector responsivity.

## Technical Information



Typical InGaAs Detector Response Curve



;