

[See all 21 Products in Family](#)

Laser ZX20 660nm 100mW, 30° (Recertified 05-P)



Stock **#19-434-RCD-05P** RECERTIFIED **1 In Stock**

-

1

+

£1,100^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	£1,100.00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads



General

Laser Class - IEC:	
3R	
Note:	
Power Supply: #24-361	
M12 Cable: #64-836	
Style:	
Homogeneous Line	
Manufacturer:	
Z-Laser	

Diode	Type of Laser:
	Laser Class - CDRH:
IIIa	
Physical & Mechanical Properties	
90	Weight (g):
97	Housing Length (mm):
20	Housing Diameter (mm):
<0.8	Bore Sighting (mrad):
<10	Pointing Stability (µrad/°C):
Optical Properties	
660.00	Wavelength (nm):
Red	Color:
30.00	Fan Angle (°):
100mm to Collimation	Focus Range (mm):
Electrical	
100	Output Power (mW):
±3	Power Stability (%):
400	Modulation Frequency (kHz):
Hardware & Interface Connectivity	
Free Space	Output Type:
5 pins, M12	Connector:
5 - 30 DC	Input Voltage (V):
Environmental & Durability Factors	
-10 to +50	Operating Temperature (°C):
-40 to +85	Storage Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Homogenous Intensity Distribution Lines with Fan Angles from 20° to 90°
- IP67 Rated Stainless Steel Housing
- Violet, Blue, Green, and Red Wavelengths Available

Z-Laser ZX20 Focusable Machine Vision Laser Diode Modules feature even-intensity distribution lines in wavelengths from 405 – 660nm for demanding image processing applications. The IP67 rated, stainless steel housings are shock and vibration proof, enabling these laser diode modules to be used in harsh industrial environments. Manually focusable without any additional tools, Z-Laser ZX20 Focusable Machine Vision Laser Diode Modules are ideal for use in measurement and alignment in machine vision, 3D measurement, positioning, and triangulation applications. Additional features include 400kHz TTL modulation for camera synchronization, analog modulation for output power adjustment, and a serial interface for monitoring temperature, laser usage, and failure codes.

Note: M12 connection cable [#64-836](#) is recommended for ease of system integration.

Red wavelengths (640 and 660nm) are most commonly used in machine vision applications, as the quantum efficiency of most camera sensors are optimized for this wavelength range. Violet (405nm), blue (450nm), and green (520nm) are most commonly used with semi-transparent surfaces or with highly reflective surfaces such as polished metal and solder joints. These wavelengths can also be used to create visual contrast on glowing materials such as molten steel.