

[See all 16 Products in Family](#)

LUCID Vision Labs Helios™2 Wide Time of Flight (ToF) Camera

See More by [LUCID Vision Labs™](#)



Stock #28-888 [CONTACT US](#)

⊖ 1 ⊕ £1,436⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£1,436.00 each
Need More?	Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Product Downloads

Monochrome **Spectrum:**

General

Monochrome Camera **Type:**

HTW003S-001 **Model Number:**

Lucid Vision Labs **Manufacturer:**

Helios™

Camera Series:

108 x 78

Field of View (°):

Physical & Mechanical Properties

Dimensions (mm):
60 x 60 x 77.5 (excludes connectors and lens mount)

Weight (g):
390

Housing:
Full

Field of View (mm):
13.8 x 8.1

Sensor

Sensor Format:
1/2"

Resolution (Megapixels):
0.30

Frame Rate (fps):
30.00

Pixels (H x V):
640 x 480

Pixel Size, H x V (µm):
10 x 10

Sensing Area, H x V (mm):
0.64 x 0.48

Imaging Sensor:
Sony DepthSense IMX556

Type of Sensor:
Progressive Scan CMOS

Shutter Type:
Global

Pixel Depth:
8/12/16 bit

Exposure Time:
62.5 µs, 250 µs, or 1000 µs

Dynamic Range (dB):
Standard

Machine Vision Standard:
GigE Vision v2.0

Electrical

Power Consumption (W):
12 - 30

Hardware & Interface Connectivity

Interface:
GigE (PoE+)

Connector:
GigE, M12

Power Supply:
Power over Ethernet (PoE) or via GPIO with 12-24VDC Power Supply

GPIOs:
1 opto-isolated input, 1 opto-isolated output, 2 non-isolated bi-directional ports

Synchronization:
Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588)

Interface Port Orientation:
Back Panel

GPIO Connector Type:
8-pin MB

Environmental & Durability Factors

Operating Temperature (°C):
-20° to 50°C

Storage Temperature (°C):
-20° to 50°C

Regulatory Compliance

Certificate of Conformance:
[View](#)

Product Details

- Ideal for Robotics and Automation Applications
- IP67 Rated 3D Cameras
- Available Kits Feature 3D and 2D RGB Solutions

LUCID Helios™2 Time of Flight (ToF) Cameras are 3D cameras featuring Sony's DepthSense sensor, engineered for high performance operation in industrial environments. Built for demanding 24/7 environments, these cameras are ideal for robotics, 3D inspection, advanced material handling, sorting and pick and place applications. LUCID Helios™2 Time of Flight (ToF) Cameras feature enhanced calibration between the VCSELs and sensor timing, resulting in higher 3D detail, along with improved edge detection to reduce flying pixels and overall noise. For an even higher performance option, the Helios™2+ offers high dynamic range and high-speed modes for precise and quick analyzation. Available kits feature a Helios™2 ToF Camera, 3.2MP Triton Camera, lens tubes, cables, and accessories required for creating dust proof, water-resistant color point clouds.

;