

LUCID Vision Labs Triton™ TRI064S-MC, Sony IMX178, 6.3MP, Monochrome Camera

See More by [LUCID Vision Labs™](#)



LUCID Vision Labs Triton™ Power over Ethernet (PoE) Cameras



Stock **#13-717** **1 In Stock**

[Similar Cameras](#)

-

1

+

£321⁶⁰

ADD TO CART

Volume Pricing	
Qty 1+	£321.60 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:

Monochrome Camera	
TR1064S-MC	Model Number:
Lucid Vision Labs	
Manufacturer:	
Triton™	Camera Series:
Monochrome	
Spectrum:	
Physical & Mechanical Properties	
Dimensions (mm):	
29 x 29 x 45 (excludes connectors and lens mount)	
Weight (g):	
67	
Housing:	
Full	
Sensor	
Image Buffer:	
128MB	
Sensor Format:	
1/1.8"	
Resolution (Megapixels):	
6.30	
Frame Rate (fps):	
19.50	
Pixels (H x V):	
3,072 x 2,048	
Pixel Size, H x V (µm):	
2.40 x 2.40	
Sensing Area, H x V (mm):	
7.37 x 4.92	
Imaging Sensor:	
Sony IMX178	
Type of Sensor:	
Progressive Scan CMOS	
Shutter Type:	
Rolling	
Pixel Depth:	
12 bit	
Exposure Time:	
30µs - 10s	
Dynamic Range (dB):	
71.93	
Machine Vision Standard:	
GigE Vision v2.0	
Electrical	
Power Consumption (W):	
2.5 (External Power Supply) 3.1 (PoE)	
Hardware & Interface Connectivity	
Interface:	
GigE (PoE)	
Connector:	
GigE, M12	
Power Supply:	
Power Supply Required and Sold Separately. USA: #18-364 Europe: #18-364 Japan: #18-364 Korea: Not Available China: #18-364	
GPIOs:	
1 opto-isolated input, 1 opto-isolated output, 2 non-isolated bi-directional ports	
Synchronization:	
Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588)	
Interface Port Orientation:	
Back Panel	
GPIO Connector Type:	
8-pin M8	
Threading & Mounting	

C-Mount	Mount:
1/4-20 with Tripod Mount Adapter	Mounting Threads: #11-474
Environmental & Durability Factors	
-20 to +55	Operating Temperature (°C):
-30 to +60	Storage Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Compact 29 x29 x45mm Form Factor
- Global, Rolling, or Polarized CMOS Sensors
- IP67 Protection with Optional Lens Tubes

LUCID Vision Labs Triton™ GigE Power over Ethernet (PoE) Cameras provide exceptional price performance in a compact 29 x29mm form factor. These cameras are available with Sony's Pregius™ and Starvis™ imaging sensors with up to 24.5 megapixels of resolution, as well as Sony's polarized sensor. Each imaging sensor is actively aligned during manufacturing, ensuring sharp and crisp images even in the corners. Using the accessory IP67 lens tubes (sold separately), LUCID Vision Labs Triton GigE Power over Ethernet (PoE) Cameras can operate in harsh environments where dust or water are present up to IP67 thresholds. Triton cameras are ideal for automotive, process control, and food and beverage applications.