

[See all 11 Products in Family](#)

## M35.5 x 0.5 to M25.5 x 0.5 Adapter

See More by [Advanced Illumination](#)



#88-494: M35.5 x 0.5 to M25.5 x 0.5 Adapter

Stock **#88-494** [CONTACT US](#)

⊖ 1 ⊕ £88<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	£88.00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

### Product Downloads

### General

Accessory **Type of Illumination:**

### Regulatory Compliance

[Compliant](#)

RoHS 2015:

## Product Details

- Slim Profile to Ease System Integration
- High Brightness LEDs
- Multiple Size, Wavelength, and Working Distance Options

Advanced Illumination High Intensity Ring Lights utilize an arrangement of high brightness LEDs to precisely illuminate a wide variety of imaging applications. Advanced Illumination High Intensity Ring Lights feature a slim profile to ease system integration, and are available in a variety of sizes, wavelengths, and working distance options. A manual intensity adjustment option is also available for added flexibility. 4.6" and 6" models are IP67 compliant. An adapter is also available for mounting the 2.95" ring light to M25 x 0.5 lenses.

**Note:** Required 24V power supply [#66-855](#). [Accessories for Advanced Illumination products](#) are available and sold separately.

### 3D-Printable Mount Files



Ring Light Configuration

[Download Now](#)

Designed for use with the [Articulating Arm Mounting Systems](#), these 3D-printed mounts allow easy positioning of lights in brightfield or darkfield setups. The design is based on mounting illumination to 1/4-20" breadboards or into 80/20 extrusion systems, but can be adapted based on user needs. Mounts are available for ring, bar, line, and inline spot lights.



#### Application Note

Illumination Mounts for Machine Vision Applications

[Read](#)



#### Video

Assembly of 3D Printed Mounts for Common Illumination Geometries

[Watch](#)

