

[See all 13 Products in Family](#)

## M49 x 0.75 Mounted Linear Glass Polarizing Filter



Mounted Linear Glass Polarizing Filters

Stock **#25-085** [CONTACT US](#)

⊖ 1 ⊕ £53<sup>20</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-9	£53.20 each
Qty 10-25	£50.80 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Mounted Imaging Filter **Type:**

### Physical & Mechanical Properties

44.50 **Clear Aperture CA (mm):**

51.60 **Diameter (mm):**

Dichroic **Construction:**

## Optical Properties

Uncoated **Coating:**

Extinction Ratio:  
Approx. 19:1 at 400nm  
Approx. 200:1 at 500nm  
≥2700:1 at 550-650nm  
Approx. 600:1 at 700nm

Float Glass **Substrate:** □

95% Efficiency **Polarization:**

Transmission (%):  
Single: 30  
Crossed: 0.15

Wavelength Range (nm):  
400 - 700

## Threading & Mounting

M49 x 0.75 **Filter Thread:**

6.80 **Mount Thickness (mm):**

## Environmental & Durability Factors

-15 to +70 **Operating Temperature (°C):**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Stackable, Rotating Mount for Easy Integration into Imaging Systems
- Eliminate Hot Spots and Reduce Glare
- 95% Polarization Efficiency
- Also Available [Unmounted](#)

Mounted Linear Glass Polarizing Filters feature a rotatable threaded mount available in a wide range of standard thread sizes. Linear polarizing filters will transmit a single axis of polarization and can be used to reduce glare and hot spots in imaging systems. Two polarizing filters can be stacked to achieve a variable density effect. Thickness includes a 2mm male thread. Mounted Linear Glass Polarizing Filters have 95% polarization efficiency. The filters are also available [unmounted](#).

## Technical Information

