

MT-4 Accessory Tube Lens

See More by [Mitutoyo](#)



Stock **#54-428** **8 In Stock**

-

1

+

£692⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£692.00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

MT-4

Model Number:

Tube Lens


Type:

Physical & Mechanical Properties	
34.00	Diameter (mm):
27.00	Length (mm):
Optical Properties	
200.00	Focal Length FL (mm):
1X	Magnification:
436 - 656	Wavelength Range (nm):
24.00	Field Number (mm):
11.2	Entrance Pupil Diameter (mm):
Threading & Mounting	
26mm x0.706 mm pitch	Mounting Threads:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

PRODUCT DETAILS

- Creates an Image When Used With a Mitutoyo Objective
 - Low Cost Alternative to [Mitutoyo VMU](#) and [FS-70 Microscopes](#)
 - [Accessory Adapters](#) Available to Ease Integration with C-Mount Cameras
- Mitutoyo Tube Lenses function as secondary lenses to form an image using any of the [Mitutoyo Infinity Corrected Objectives](#). They are economical alternatives to the [FS70 Microscope](#) or [Infinitube® In-line Assembly Unit](#). Several options are available, depending upon system requirements. The MT-4 and MT-40 are designed for end-user integration and can easily be used with any C-Mount camera with our Mitutoyo C-Mount Camera Extension Tube [#56-992](#). Mitutoyo Tube Lenses MT-4 Tube Lens is recommended for use with Objectives from 1X to 20X magnification, while the MT-40 is recommended for use with Objectives with >20X magnification. The MT-1 Tube Lens permits the introduction of a beamsplitter to the imaging path, allowing for a custom in-line illumination system. The MT-2 Tube Lens is similar to the MT-1 but with an effective focal length of 400mm, providing twice the stated magnification for any of the Mitutoyo objectives. The MT-L and MT-L4 lenses are designed for the [M Plan NUV](#) and [M Plan UV](#) series of objectives, respectively. [NIR and zoom tube lenses](#) are also available through our line of Precision Zoom Lenses.

TECHNICAL INFORMATION



MT-4 (#54-428)

Intermediate image position

