

[See all 6 Products in Family](#)

Optotune ICC-4C-2000 Extension Kit

See More by [Optotune](#)



Optotune ICC-4C-2000 Extension Kit (#23-718)

Stock **#23-718** **1 In Stock**

⊖ 1 ⊕ £208⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1+ | £208.00 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Extension Kit **Type:**

Contents of Kit:
 Adapter board for XPRs, BSW and FMR (with 20 cm extension cable)
 Micro-USB cable
 DIN Rail clamp kit

Regulatory Compliance

Product Details

- ICC-1C for Control of a Single Optotune Lens
- ICC-4C-500 Controls Up to 4 Optotune Lenses Simultaneously
- ICC-4C-2000 Controls Optotune Beam Shifters and Fine Steering Mirrors
- Driven via Optotune Cockpit GUI, SDK, or Analog Signal
- [Optotune Lens Drivers](#) and [Gardasoft Controllers](#) Also Available

Optotune ICC Current Controllers allow for control of Optotune Focus Tunable Lenses delivering ± 500 mA of current (up to 4 lenses can be controlled with [ICC-4C-500](#)), or of Optotune's Beam Shifters and Fine Steering Mirrors ([ICC-4C-2000](#)). The controller features a variety of interfaces to facilitate easy communication with existing machine vision systems, including USB, UART, I2C, Ethernet, and analog input. The Optotune Cockpit GUI is used to easily drive the controller over USB or ethernet with Python and C# SDKs available for further user integration. Optotune ICC Current Controllers are ideal for machine vision applications and for using multiple liquid lenses to simplify control and wiring. These controllers also offer the ability to control LEDs, laser diodes, thermo-electric coolers (TECs), or other devices requiring accurate current control. The extension kit [#22-409](#) is required for driving Optotune Focus Tunable Lenses with FPC connectors using the [ICC-1C](#) or [ICC-4C-500](#), and the extension kit [#23-718](#) is required for driving Beam Shifters and Fine Steering Mirrors with the [ICC-4C-2000](#).

Technical Information

| OPTOTUNE ICC-4C-500 CONTROLLER PRODUCTS | | | |
|---|--------------------------|--|--|
| Stock Number | Description | Contents | Notes |
| #22-408 | ICC-4C-500 Controller | <ul style="list-style-type: none"> • ICC-4C-500 Controller only | Used to control up to 4 Optotune lenses with Hirose connectors simultaneously (up to ± 500 mA per channel). Power supply sold separately and required (#22-410). To control Optotune lenses with FPC connectors, #22-409 is also required. For I/O input, users must supply their own I/O connector. |
| #22-409 | ICC-4C-500 Extension Kit | <ul style="list-style-type: none"> • Adaptor board for lenses (with 30 cm extension cable) • Micro-USB cable • DIN Rail clamp Kit | Used with the ICC-4C-500 Controller (#22-408) to control up to 4 Optotune lenses with FPC connectors simultaneously. Plugs directly into the auxiliary output connector, or with included extension cable. |
| #22-410 | ICC-4C Power Adapter | <ul style="list-style-type: none"> • Power adapter with US main cable | Includes AC/DC adapter that interfaces with the ICC-4C and US main cable. |

| OPTOTUNE ICC-4C-2000 CONTROLLER PRODUCTS | | | |
|--|---------------------------|---|--|
| Stock Number | Description | Contents | Notes |
| #23-717 | ICC-4C-2000 Controller | <ul style="list-style-type: none"> • ICC-4C-2000 Controller only | Used to control Optotune's XPR Beam Shifters, BSW-20 Beam Shifters , and FMR-20 Fine Steering Mirrors . Provides 4 independent channels with ± 2 A per channel. Power supply and extension kit sold separately and required (#23-718 and #22-410). For I/O input, users must supply their own I/O connector. |
| #23-718 | ICC-4C-2000 Extension Kit | <ul style="list-style-type: none"> • Adapter board for XPRs, BSW and FMR (with 20 cm extension cable) • Micro-USB cable • DIN Rail clamp Kit | Used with the Optotune ICC-4C-2000 controller to interface with XPR, BSW-20, and FMR-20 products through FPC interface. Plugs directly into the 34-pin output connector, or with included extension cable. |
| #22-410 | ICC-4C Power Adapter | <ul style="list-style-type: none"> • Power adapter with US main cable | Includes AC/DC adapter that interfaces with the ICC-4C and US main cable. |