

[See all 21 Products in Family](#)

## Oryx® ORX-10GS-89S6M-C Mono 10GigE (Recertified 05-P)

See More by [Teledyne FLIR](#)



ORYX-10G-310S9C



Stock #19-792-RCD-05P **RECERTIFIED** 1 In Stock

[Similar Cameras](#)

- 1 + £3,596.00

**ADD TO CART**

Volume Pricing

Qty 1+	£3,596.00 each
--------	----------------

Volume Pricing	
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

## Product Downloads

Monochrome

**Spectrum:**

## General

Monochrome Camera

**Type:**

ORX-10GS-89S6M-C

**Model Number:**

FLIR

**Manufacturer:**

Oryx®

**Camera Series:**

## Physical & Mechanical Properties

60 x 60 x 64

**Dimensions (mm):**

386

**Weight (g):**

Full

**Housing:**

## Sensor

240MB

**Image Buffer:**

1"

**Sensor Format:**

8.90

**Resolution (Megapixels):**

93.00

**Frame Rate (fps):**

4,096 x 2,160

**Pixels (H x V):**

3.45 x 3.45

**Pixel Size, H x V (µm):**

14.13 x 7.45

**Sensing Area, H x V (mm):**

Sony IMX255

**Imaging Sensor:**

Progressive Scan CMOS

**Type of Sensor:**

Global

**Shutter Type:**

8/10/12 Bit

**Pixel Depth:**

5µs - 30s

**Exposure Time:**

71.57

**Dynamic Range (dB):**

GigE Vision

**Machine Vision Standard:**

## Electrical

12.6

**Power Consumption (W):**

## Hardware & Interface Connectivity

10GigE

**Interface:**

GigE interface with Screw Locks

**Connector:**

**Power Supply:**

Power Supply Required and Sold Separately.

USA: [#19-803](#)

Europe: [#19-803](#)

Japan: [#19-803](#)

Korea: Not Available

China: [#19-803](#)

**GPIOs:**  
2 opto-isolated inputs, 2 opto-isolated outputs, 2 non-isolated bi-directional

**Synchronization:**  
Hardware Trigger (GPIO) or Software Trigger

**Interface Port Orientation:**  
Back Panel

**GPIO Connector Type:**  
12-pin Hirose (HR10)

## Threading & Mounting

**Mount:**  
C-Mount

**Mounting Threads:**  
1/4-20 with Tripod Mount Adapter [#19-804](#)

## Environmental & Durability Factors

**Operating Temperature (°C):**  
0 to +70

**Storage Temperature (°C):**  
-30 to +60

## Regulatory Compliance

**Certificate of Conformance:**  
[View](#)

## Product Details

- 10GBASE-T (10GigE) Ethernet Interface
- 3.2 to 31 Megapixel Sony 4th Gen Pregius S Sensors
- Supports 4K60, 12-bit System Integration
- Tripod Adapter Built into Larger Oryx® Models



### Teledyne FLIR IIS Oryx 10GigE: High throughput, Award-winning camera designs

Reliably capture images at high speed

The **Oryx 10GigE** camera family supports transfer speeds of up to 10 Gbit/s enabling capture of 4K resolution, 12-bit images at speeds exceeding 60 FPS. Reliable image transfer at high bandwidth is further improved with Myricom bundles and packet resend feature. A range of sensor options offer resolutions from 3.2 Megapixel up to 31 Megapixel. Oryx features include IEEE1588 clock synchronization and full compatibility with several popular third-party software supporting GigE Vision. Oryx's 10GBASE-T interface is a proven and widely deployed standard that provides reliable image transfer at cable lengths over 50 meters on inexpensive CAT6A, and up to 30 meters on CAT5e.

**Note:** The ORX-10G-310S9 and ORX-10G-245S8 cameras require an F-Mount lens adapter (sold separately).

#### Features

- Color or monochrome sensors
- Various frame triggering options including up to 8 sets of 2-feature sequencer
- Pixel binning, decimation, ROI
- On camera image processing includes Gamma, LUT, and sharpness

#### Applications

- Stadium venues
- Site security
- Factory automation
- Traffic monitoring
- Inspection systems