

[See all 43 Products in Family](#)

## Power Supply for 1.5-2.0mW HeNe Laser, AC, US Plug



Benchtop Power Supply, AC Input (Front)



Stock **#11-387** 1 In Stock

-

1

+

£660<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | £660.00 each                  |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads



### General

Type:

Benchtop

Compatible Laser Models:

1101, 1101P, 1103, 1103P

Model Number:

SL92 Series

Compatible Laser Stock Number:  
#62-718, #62-719, #64-103, #64-104

Features:  
Turn Key, CDRH Delay (3-5 seconds)

Physical & Mechanical Properties

9.00 x 5.50 x 2.38      Dimensions (inches):

Electrical

8.33      Output Power (W):

0.55/0.32      Input Current (A):

Hardware & Interface Connectivity

1700      Output Voltage (V):

4.9      Output Current (mA):

High Voltage Alden Connector      Connector:

100/110/220 (AC)      Input Voltage (V):

Regulatory Compliance

[View](#)      Certificate of Conformance:

Product Details

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

**Note:** Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

Technical Information

Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

