

Power Supply for 15-22.5mW HeNe Laser, AC, US Plug



Benchtop Power Supply, AC Input (Front)



Stock #11-391 **8 In Stock**

1 **£864.00**

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1+ | £864.00 each |
| Need More? | Request Quote |

Prices shown are exclusive of VAT/local taxes

Product Downloads



General

Type:
Benchtop

Compatible Laser Models:
[1144](#), [1144P](#), [1145P](#), [1145](#)

Model Number:
SL93 Series

Compatible Laser Stock Number:
[#62-728](#), [#62-729](#), [#62-731](#), [#62-732](#)

Features:
Turn Key, CDRH Delay (3-5 seconds)

Physical & Mechanical Properties

Dimensions (inches):
9.00 x 5.50 x 2.38

Electrical

Output Power (W):
24.7

Input Current (A):
0.60/0.30

Hardware & Interface Connectivity

Output Voltage (V):
3800

Output Current (mA):
6.5

Connector:
High Voltage Alden Connector

Input Voltage (V):
100/110/220 (AC)

Regulatory Compliance

Certificate of Conformance:
[View](#)

Product Details

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

Note: Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

Technical Information

Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

□