

Sectional LED Ring Light, 220V



Stock **#68-770** 1 In Stock

-

1

+

£208^{.00}

ADD TO CART

Volume Pricing	
Qty 1-5	£208.00 each
Qty 6+	£187.20 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
72.00	Number of LEDs:
LED Illuminator	Type of Illumination:
Note:	
Power Supply Included Requires 110V to 220V Inversion for Use in the US	
Ring Light	Geometry:

Constant	Illumination Mode:
Physical & Mechanical Properties	
60.5	Inner Diameter (mm):
Optical Properties	
White	Color:
Hardware & Interface Connectivity	
220.00	Operating Voltage (V):
Environmental & Durability Factors	
6400.00	Color Temperature (K):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Large Inner Diameters for Easy Mounting
- 6400K Color Temperature
- Features Sectional Light Control

LED Ring Light Illuminators are strong alternatives to traditional fluorescent ring lights. The sectional ring light features lighting control in each of the unit's four quadrants, a 60.5mm inner diameter, and 72 LEDs. The sectional ring light is controlled using a panel on the top of the unit. LED Ring Light Illuminators are ideal for use with reflective parts and features a 70mm inner diameter and 60 LED bulbs. Sectional Light Control and Polarizer/Analyzer models are available.

Note: Due to CE restrictions, [#68-771](#) Polarizer/Analyzer LED Ring Light is not available in all regions. Please [contact us](#) for a suitable replacement.