

[See all 2 Products in Family](#)

White LED Spot Light



Stock #63-339 CLEARANCE **5 In Stock**

⊖ 1 ⊕ £335⁹⁶

ADD TO CART

Volume Pricing

Qty 1+	£335.96 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

100,000 **LED Lifetime (hours):**

LED Illuminator **Type of Illumination:**

Spot Light **Geometry:**

Strobed or Constant **Illumination Mode:**

Physical & Mechanical Properties

35.00 **Diameter (mm):**

29.5 **Height (mm):**

Optical Properties

White **Color:**

10.00 **Spot Size at 50mm Working Distance (mm):**

N/A **Irradiance at 50mm (W/m²):**

Electrical

400mA **Maximum Input Current:**

Hardware & Interface Connectivity

Power Supply:
Power Supply Required and Sold Separately.
USA: [#59-433](#)
Europe: Not Available
Japan: [#59-433](#)
Korea: Not Available
China: [#59-433](#)

Threading & Mounting

M3 **Mounting Threads:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[Compliant](#) **Reach 209:**

[View](#) **Certificate of Conformance:**

Product Details

[#59-433](#) Universal Power Supply and [#59-371](#) DC Current Controller are required for operating all spot lights. [#63-342](#) Area and Spot Light Heat Sink is recommended to maintain performance and optimize product lifetime.

- Variable Intensity with DC Current Controller
- Excellent Uniformity
- 60,000 Hour Product Lifetime
- [Heat Sinks and Power Supplies](#) Sold Separately

Compact LED Spot Lights provide the high-power illumination required in machine vision, biomedical, fluorescence, and strobing applications. Each LED module contains four M3 mounting holes on a 29mm diameter circle. The universal power supply, which accepts a 90 - 245V AC input, ships with clip-on adapters for the US, Europe, and UK. Through the DIN rail mountable DC current controller, LED intensity can be adjusted manually via a potentiometer or by supplying a 0 - 5V analog control input. The DC current controller is designed to deliver up to 400mA at 24V.

Note: [#59-433](#) Universal Power Supply and [#59-371](#) DC Current Controller are required for operating all spot lights. [#63-342](#) Area and Spot Light Heat Sink is recommended to maintain performance and optimize product lifetime.